

GALEA STAINLESS

5087PJM100P30-10

EAN 4031582383775



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Galea stainless |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Stainless | ✓ |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 139 mm |
| Overall width | 66 mm |
| Overall weight | 0.459 kg |

WHEEL

| | |
|-----------------------|--------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing, stainless |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 30 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|---|
| Material fork | Polyamide |
| Fork shape | Closed |
| Swivel bearing | Two ball races, reinforced or stainless |
| Offset | 40 mm |
| Swivel radius | 128 mm |
| Swivel interference | 256 mm |
| Dome diameter | 59 mm |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 10 mm |

GALEA STAINLESS

5087PJM100P30-10

EAN 4031582383775



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

