

NOVATECH

ETY080X20-Ø20 HL14

EAN 4031582419047



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj (RS/2RS)
Prečnik	80 mm
Širina omotac	20 mm
dimenzija rupa osovina	20 mm
dužina glavcine	14 mm
Teškoća gazećeg omotac (A)	92 Šor A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip kućišta	Tocak
Nosivost na 3 km/h	140 kg
Statički Nosivost	280 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,3 kg

TEHNIČKI CRTEŽI

