

COMPACTA

2198POI014P60-30x17

EAN 4031582435641



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	25 kg
Electric Conductive	No
Stainless	No
Load capacity Static	50 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	17 mm
Overall weight	0.01 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	14 mm
Tread width	14 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	30 mm
Plate width	17 mm
Plate hole length (Maximum)	20 mm
Plate hole width (Maximum)	20 mm
Plate hole diameter	4 mm

COMPACTA

2198POI014P60-30x17

EAN 4031582435641



BETTER MOBILITY. BETTER LIFE.

Product Drawings

