

# NOVATECH

FTP 250X80-Ø30 HL90

EAN 4031582319422  
Order number 00801280



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	80 mm
Axle hole diameter	30 mm
Hub length	90 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2160 kg
Load capacity at 6 km/h	1800 kg
Load capacity Static	3600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	9.24 kg

# NOVATECH

FTP 250X80-Ø30 HL90

EAN 4031582319422  
Order number 00801280



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

