

DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Materijal za telo	poliamid, super težak
materijal omotaca	Dupli prirubnici sa trake
Nošenje	precizini kuglični ležaj
stitnici omotaca	Bez stražara
Prečnik	50 mm
Širina omotac	26 mm
dimenzija rupa osovina	15 mm
dužina glavnice	32 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech plus
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	240 kg
Nosivost na 6 km/h	200 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	480 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C

DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370

Broj porudžbine 00860912
Product Drawings



BETTER MOBILITY. BETTER LIFE.

