

DURATECH

TOP 250x50-Ø20 HL60

EAN 4031582366266



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6205

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	1320 kg
Nosivost na 6 km/h	1100 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	2200 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1.88 kg

DURATECH


TOP 250x50-Ø20 HL60

EAN 4031582366266

Broj porudžbine 00832580
Product Drawings



BETTER MOBILITY. BETTER LIFE.




DURATECH

TOP 250x50-Ø20 HL60

EAN 4031582356266

Broj porudžbine 00431580



BETTER MOBILITY. BETTER LIFE.