

STYLEA

5920UOI065L51-10D23 ~9006/~9006

EAN 4031582310900
Order number 00074552



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	68 mm
Overall width	43 mm
Overall weight	0.092 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	White aluminium (similar RAL9006)
Wheel color	White aluminium (similar RAL9006)
Threadguards	Without threadguard
Diameter	65 mm
Tread width	8 mm
Axle hole diameter	0 mm
Hub length	0 mm
Body width	8 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	White aluminium (similar RAL9006)
Offset	25 mm
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	23 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

PRODUCT INFORMATION

STYLEA

5920UOI065L51-10D23 ~9006/~9006

EAN 4031582310900
Order number 00074552



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

