

NOVATECH

FTP 300X100-Ø40 HL120

EAN 4031582319439

Broj porudžbine 00801175



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	300 mm
Širina omotac	100 mm
dimenzija rupa osovina	40 mm
dužina glavcine	120 mm
Širina tela	100 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	3120 kg
Nosivost na 6 km/h	2600 kg
Statički Nosivost	5200 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	18,81 kg

NOVATECH

FTP 300X100-Ø40 HL120

EAN 4031582319439
Broj porudžbine 00801175



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

