

ICS

5327PJP125P52

EAN 4031582384604



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | ICS                           |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 220.46 lb                     |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | 14 °F                         |
| Temperature range (Maximum) | 104 °F                        |
| Overall height              | 6.54 in                       |

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | Integrated threadguard |
| Diameter              | 4.92 in                |
| Tread width           | 1.26 in                |
| Hardness of tread (A) | 87 Shore A             |

HOUSING

|                     |                 |
|---------------------|-----------------|
| Material            | Polyamide       |
| Fork shape          | Slim            |
| Swivel bearing      | Stem, swiveling |
| Offset              | 1.46 in         |
| Swivel interference | 7.83 in         |

FITTING

|                             |                                         |
|-----------------------------|-----------------------------------------|
| Fitting type                | Rectangular plate, US-bolt hole spacing |
| Plate length                | 3.74 in                                 |
| Plate width                 | 2.76 in                                 |
| Plate hole length (Minimum) | 1.75 in                                 |
| Plate hole length (Maximum) | 2.05 in                                 |
| Plate hole width (Minimum)  | 2.83 in                                 |
| Plate hole width (Maximum)  | 2.99 in                                 |
| Plate hole diameter         | 0.43 in                                 |



# ICS

5327PJP125P52



EAN 4031582384604



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---



IF  
Design  
Award