

AGILA

2470PJO100R47-21,5/24

EAN 4031582324907



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Electric conductive	no
Stainless	no
Load capacity Static	352.74 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	5.31 in
Overall width	2.36 in
Overall weight	1.45 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	1.5 in
Swivel radius	3.46 in
Swivel interference	6.93 in
Dome diameter	2.36 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.26 in
Body width	1.26 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Synthetic expander, square
Stem length	0.94 in
Expander fitting (Minimum)	0.87 in
Expander fitting (Maximum)	0.94 in
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2470PJO100R47-21,5/24

EAN 4031582324907

Order number 00061718

Product Drawings



BETTER MOBILITY. BETTER LIFE.

