

SUPRATECH

PJP125X40-Ø 8,3, BLUE

EAN 4031582444216



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (A)	65 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	180 kg
Load capacity Static	360 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.24 kg

SUPRATECH

PJP125X40-Ø 8,3, BLUE

EAN 4031582444216



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

