

SUPRATECH

5440PJP100R05-32

EAN 4031582336757



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Supratech |
| Housing type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 139 mm |
| Overall weight | 0.799 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Polyamide |
| Fork shape | Broad |
| Swivel bearing | Precision ball bearing |
| Offset | 38 mm |
| Swivel radius | 88 mm |
| Swivel interference | 176 mm |

FITTING

| | |
|---------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 32 mm |
| Bolt length | 45 mm |

SUPRATECH

5440PJP100R05-32

EAN 4031582336757



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

