

ELASTECH

UFP100x34-Ø8

EAN 4031582338690



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	34 mm
Axle Hole Diameter	8.3 mm
Hub Length	45 mm
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.29 kg

ELASTECH

UFP100x34-Ø8

EAN 4031582338690

Order number 00031810
Product Drawings



BETTER MOBILITY. BETTER LIFE.

