

# AGILA TWIN

2970PIO075P30-10

EAN 4031582362268



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila twin                |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 80 kg                     |
| Load capacity Static        | 160 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall height              | 99 mm                     |
| Overall weight              | 0.457 kg                  |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 75 mm                     |
| Tread width           | 25 mm                     |
| Hardness of tread (A) | 80 Shore A                |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel bearing      | Two ball races      |
| Offset              | 31.4 mm             |
| Swivel radius       | 68.9 mm             |
| Swivel interference | 137.8 mm            |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 10 mm     |

# AGILA TWIN

2970PIO075P30-10

EAN 4031582362268



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

