

ZETA REVERSE

468SUAC160P63

EAN 4031582396386
Order number 00860876



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Zeta reverse
Housing type	Swivel castor with spring loaded directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	771.62 lb
Load capacity at 3.7 mph	617.29 lb
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall width	3.78 in
Overall weight	6.48 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.57 in
Body width	1.57 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Color	Blue passivated
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Dome diameter	3.78 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

ZETA REVERSE

468SUAC160P63

EAN 4031582396386
Order number 00860876



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

