

DURATECH

TOP 082X66-Ø20 HL66

EAN 4031582331042
Broj porudžbine 00827823

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stičnici omotaca	Bez stražara
Prečnik	82 mm
Širina omotac	66 mm
dimenzija rupa osovina	20 mm
dužina glavcine	66 mm
Širina tela	66 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

PERFORMANSE

Performanse kotrljanja ● ● ● ● ●

Buka u pokretu ● ● ● ● ●

Ishrana ● ● ● ● ●

otpornost na rdju ● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	650 kg
Nosivost na 6 km/h	520 kg
Statički Nosivost	1300 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,462 kg

DURATECH

TOP 082X66-Ø20 HL66

EAN 4031582331042
Broj porudžbine 00827823



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

