

COMPACTA

2198UOI025P60-40X17

EAN 4031582300284
Order number 00021131



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	25 kg
Load capacity Static	50 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	28 mm
Overall width	20 mm
Overall weight	0.018 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	25 mm
Tread width	13 mm
Body width	13 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Angular
Colour	Blue passivated
Dome diameter	20 mm

FITTING

Fitting type	Rectangular plate
Plate length	40 mm
Plate width	17 mm
Plate hole length (Maximum)	30 mm
Plate hole width (Maximum)	30 mm
Plate hole diameter	4.5 mm

COMPACTA

2198UOI025P60-40X17

EAN 4031582300284
Order number 00021131



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

