PRODUCT INFORMATION

# ALPHA STAINLESS

8478PID125P62

EAN 4031582381702

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●●● |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Alpha stainless |
| Type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 100 kg |
| Electric Conductive | No |
| Stainless | Yes |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 155 mm |
| Overall width | 85 mm |
| Overall weight | 0.83 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Stainless steel, heavy |
| Fork shape | Broad |
| Housing Color | Stainless steel |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Solid rubber, non-marking |
| Bearing | Roller bearing, stainless |
| Axle | Screwed with nut |
| Wheel Color | Graphite black (RAL9011) |
| Diameter | 125 mm |
| Tread width | 37 mm |
| Body width | 37 mm |
| Hardness of tread (A) | 80 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Small rectangular plate |
| Plate length | 100 mm |
| Plate width | 85 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 60 mm |
| Plate hole width (Minimum) | 77 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 9 mm |

© Copyright 2026 TENTE International GmbH


# ALPHA STAINLESS


8478PID125P62

EAN 4031582381702

Order number 00035730

**Product Drawings**




© Copyright 2026 TENTE International GmbH