

# AGILA

2477PJP150R05-28 M8/19

EAN 4031582302189  
Order number 00029364



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Type                        | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 100 kg                        |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 188 mm                        |
| Overall width               | 60 mm                         |
| Overall weight              | 1.251 kg                      |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver grey (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 150 mm                 |
| Tread width           | 32 mm                  |
| Body width            | 32 mm                  |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Colour              | Blue passivated     |
| Offset              | 36 mm               |
| Swivel radius       | 131 mm              |
| Swivel interference | 262 mm              |
| Dome diameter       | 60 mm               |

## FITTING

|                              |                   |
|------------------------------|-------------------|
| Fitting type                 | Solid stem, round |
| Bolt diameter                | 28 mm             |
| Bolt length                  | 45 mm             |
| Bolt thread position         | 19 mm             |
| Bolt mounting holes quantity | 2                 |

# AGILA

2477PJP150R05-28 M8/19

EAN 4031582302189  
Order number 00029364



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

