

AGILA

2470UAK050P30-11

EAN 4031582301083



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Agila
CO2 emission (scope 3)	0.78
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall Height	69 mm
Overall width	43 mm
Overall weight	0.19 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	24 mm
Swivel radius	49 mm
Swivel interference	98 mm
Dome diameter	41 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Cone ball bearing
Wheel Color	Slate grey (RAL7015)
Threadguards	With threadguard
Diameter	50 mm
Tread width	20 mm
Body width	20 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

AGILA

2470UAK050P30-11

EAN 4031582301083

Order number 00004015

Product Drawings



BETTER MOBILITY. BETTER LIFE.

