

DURATECH

MOP 200x80-Ø40 HL90

EAN 4031582320060



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	80 mm
dimenzija rupa osovina	40 mm
dužina glavnice	90 mm
Širina tela	80 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6308

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Emisija CO2 (obuhvat 3)	29.11
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	5400 kg
Nosivost na 6 km/h	4500 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	9000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	3.86 kg

DURATECH


MOP 200x80-Ø40 HL90

EAN 4031582320060

Broj porudžbine 00830849
Crteži proizvoda



BETTER MOBILITY. BETTER LIFE.




DURATECH

MOP 200x80-Ø40 HL90

EAN 4031582320060

Broj porudžbine 00836849



BETTER MOBILITY. BETTER LIFE.