

SUPRATECH

PJP200X45-Ø12,2 HL60

EAN 4031582444209



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 45 mm |
| Axle hole diameter | 12 mm |
| Hub length | 60 mm |
| Hardness of tread (A) | 65 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Supratech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 250 kg |
| Load capacity Static | 500 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 0.24 kg |

SUPRATECH

PJP200X45-Ø12,2 HL60

EAN 4031582444209



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

