PRODUCT INFORMATION

ALPHA

3478BOG100P62 TFR

EAN 4031582390643



Image may differ from the original product

PERFORMANCE

Roll Performance	●●○○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Alpha
Type	Fixed caster
Standard	EN12532 - Transport Equipment
Electric conductive	Yes
Stainless	no
Load capacity Static	661.39 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall height	5.04 in
Overall weight	1.21 lb

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Housing Color	Blue passivated

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Diameter	3.94 in
Tread width	1.38 in
Hardness of tread (D)	85 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	4.06 in
Plate width	3.35 in
Plate hole diameter	0.35 in

© Copyright 2026 TENTE International GmbH

ALPHA


3478BOG100P62 TFR

EAN 4031582390643

BETTER MOBILITY. BETTER LIFE.

Product Drawings

Platte 3470-080P62-105x80



© Copyright 2026 TENTE International GmbH