PRODUCT INFORMATION

AGILA

2478UAP050P41-55

EAN 4031582404326

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Agila
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	69 mm
Overall width	35 mm
Overall weight	0.11 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	27 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Precision ball bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Square plate
Plate length	55 mm
Plate width	55 mm
Plate hole length (Minimum)	38.5 mm
Plate hole length (Maximum)	44 mm
Plate hole width (Minimum)	38.5 mm
Plate hole width (Maximum)	44 mm
Plate hole diameter	6.3 mm

© Copyright 2026 TENTE International GmbH


AGILA


2478UAP050P41-55


EAN 4031582404326

Order number 00039979

Product Drawings







© Copyright 2026 TENTE International GmbH