

ALPHA

3470UAR100P62

EAN 4031582304268
Order number 00029587



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha |
| Type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 150 kg |
| Load capacity Static | 300 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 128 mm |
| Overall width | 75 mm |
| Overall weight | 0.805 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Colour | Blue passivated |
| Offset | 40 mm |
| Swivel radius | 90 mm |
| Swivel interference | 180 mm |
| Dome diameter | 75 mm |

FITTING

| | |
|-----------------------------|-------------------------|
| Fitting type | Small rectangular plate |
| Plate length | 105 mm |
| Plate width | 80 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 60 mm |
| Plate hole width (Minimum) | 77 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 9 mm |

ALPHA

3470UAR100P62



EAN 4031582304268
Order number 00029587



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

3470U00100P62-neu



Platte 3470-080P62-105x80

