

# COMPACTA

2198UOI045P60-67x24

EAN 4031582030075



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Compacta                    |
| Type                        | Fixed caster                |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph    | 88.18 lb                    |
| Electric conductive         | no                          |
| Stainless                   | no                          |
| Load capacity Static        | 176.37 lb                   |
| Temperature range (Minimum) | -13 °F                      |
| Temperature range (Maximum) | 176 °F                      |
| Overall height              | 1.91 in                     |
| Overall width               | 0.79 in                     |
| Overall weight              | 0.14 lb                     |

## HOUSING

|                  |                     |
|------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape       | Angular             |
| Housing Color    | Blue passivated     |
| Dome diameter    | 0.79 in             |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread material        | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Wheel color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 1.77 in                        |
| Tread width           | 0.71 in                        |
| Body width            | 0.71 in                        |
| Hardness of tread (D) | 75 Shore D                     |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 2.64 in           |
| Plate width                 | 0.94 in           |
| Plate hole length (Maximum) | 2.13 in           |
| Plate hole width (Maximum)  | 2.13 in           |
| Plate hole diameter         | 0.21 in           |

# COMPACTA

2198UOI045P60-67x24

EAN 4031582030075

Order number 00021141

Product Drawings



BETTER MOBILITY. BETTER LIFE.

