PRODUCT INFORMATION

# COMPACTA

## 2198UOI045P60-67x24

EAN 4031582030075

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Compacta |
| Type | Fixed caster |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 88.18 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 176.37 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 1.91 in |
| Overall width | 0.79 in |
| Overall weight | 0.14 lb |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Angular |
| Housing Color | Blue passivated |
| Dome diameter | 0.79 in |

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 1.77 in |
| Tread width | 0.71 in |
| Body width | 0.71 in |
| Hardness of tread (D) | 75 Shore D |

### FITTING

| | |
|---|---|
| Fitting type | Rectangular plate |
| Plate length | 2.64 in |
| Plate width | 0.94 in |
| Plate hole length (Maximum) | 2.13 in |
| Plate hole width (Maximum) | 2.13 in |
| Plate hole diameter | 0.21 in |

© Copyright 2026 TENTE International GmbH


# COMPACTA

2198UOI045P60-67x24

EAN 4031582030075

Order number 00021141

**Product Drawings**




© Copyright 2026 TENTE International GmbH