

ALPHA SMART STAINLESS

8377IDC100P30-13

EAN 4031582494020



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha smart stainless
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	80 kg
Stainless	✓
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall height	128 mm

WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Damping, heat resistant
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Hardness of tread (A)	75 Shore A

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Slim
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	121 mm
Swivel interference	242 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm