

# DURATECH

TOP 065X32-Ø12 HL32

EAN 4031582332315

Broj porudžbine 00829018



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stićnici omotaca	Bez stražara
Prečnik	65 mm
Širina omotac	32 mm
dimenzija rupa osovina	12 mm
dužina glavčine	32 mm
Širina tela	32 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6201

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	290 kg
Nosivost na 6 km/h	240 kg
Statički Nosivost	480 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,169 kg

# DURATECH

TOP 065X32-Ø12 HL32

EAN 4031582332315  
Broj porudžbine 00829018



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

