

NOVATECH

RK.ETP082X62-Ø47X13

EAN 4031582330397



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 1.8 mph	1322.77 lb
Load capacity Static	2645.54 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	3.23 in
Tread width	2.44 in
Hardness of tread (A)	92 Shore A
Ball bearing diameter	1.85 in
Ball bearing width	0.51 in

TECHNICAL DRAWINGS

