PRODUCT INFORMATION

DURATECH SILENT

UOT 125x40-Ø8,4 HL45

EAN 4031582338058

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing, damped
Wheel Color	Natural white
Diameter	125 mm
Tread width	40 mm
Axle Hole Diameter	8.4 mm
Hub Length	45 mm
Body width	40 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech silent
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall weight	0.38 kg

© Copyright 2026 TENTE International GmbH


DURATECH SILENT

UOT 125x40-Ø8,4 HL45

EAN 4031582338058

Order number 00033628

Product Drawings



© Copyright 2026 TENTE International GmbH