

ALPHA

3470UFR160P30-13

EAN 4031582304466
Order number 00032788



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	195 mm
Overall width	96 mm
Overall weight	2.001 kg

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Axle	Screwed with nut
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	160 mm
Tread width	46 mm
Body width	46 mm
Hardness of tread (A)	63 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm
Dome diameter	96 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA

3470UFR160P30-13

EAN 4031582304466
Order number 00032788



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

