

# KAPPA

9688TOP150P63 CL67

EAN 4031582316667  
Order number 00801475



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ○ ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Kappa                        |
| Type                        | Fixed castor                 |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph    | 2116.44 lb                   |
| Load capacity at 3.7 mph    | 1763.7 lb                    |
| Load capacity Static        | 3527.39 lb                   |
| Temperature range (Minimum) | -22 °F                       |
| Temperature range (Maximum) | 176 °F                       |
| Overall height              | 7.87 in                      |
| Overall width               | 3.86 in                      |
| Overall weight              | 7.09 lb                      |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide, heavy          |
| Tread material        | Identical with wheel body |
| Bearing               | Precision ball bearing    |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Threadguards          | Without threadguard       |
| Diameter              | 5.91 in                   |
| Tread width           | 1.97 in                   |
| Body width            | 1.97 in                   |
| Hardness of tread (D) | 75 Shore D                |

## HOUSING

|               |                                  |
|---------------|----------------------------------|
| Material      | Cast iron, or iron forged, heavy |
| Fork shape    | Broad, reinforced                |
| Color         | Blue passivated                  |
|               | ✓                                |
| Dome diameter | 3.78 in                          |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.31 in           |
| Plate width                 | 4.33 in           |
| Plate hole length (Minimum) | 2.95 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 4.13 in           |
| Plate hole diameter         | 0.43 in           |

# KAPPA

9688TOP150P63 CL67

EAN 4031582316667  
Order number 00801475



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

