

PRODUCT INFORMATION

# ELASTECH

RK.XLR 125x40-Ø20 HL44 ESD

EAN 4031582508383



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Tread hardness	soft
Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	125 mm
Tread width	40 mm
Hardness of tread (A)	63 Shore A

### PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

### CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.39 kg

# ELASTECH

RK.XLR 125x40-Ø20 HL44 ESD

EAN 4031582508383

Order number 10011100  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

## WB. XLR125x40-Ø20NL44 antistatic

