

PRODUCT INFORMATION

ELASTECH

RK.XLR 125x40-Ø20 HL44 ESD

EAN 4031582508383



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 160 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 320 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall weight              | 0.39 kg                       |

WHEEL

|                       |                     |
|-----------------------|---------------------|
| Tread hardness        | soft                |
| Body material         | Undefined           |
| Tread Material Mix    | Polypropylene, soft |
| Diameter              | 125 mm              |
| Tread width           | 40 mm               |
| Hardness of tread (A) | 63 Shore A          |

## WB. XLR125x40-Ø20NL44 antistatic

