PRODUCT INFORMATION

STEM

S70-10x35 / 11

EAN 4031582452723



Image may differ from the original product

PERFORMANCE

Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	176.37 lb
Electric conductive	no
Stainless	no
Load capacity Static	352.74 lb
Overall height	0.24 in
Overall weight	0.09 lb

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.39 in
Stem length	1.38 in

© Copyright 2026 TENTE International GmbH