

MONO

5020PJH080L51-10 ~9006/9011/9011

EAN 4031582317114



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Mono
Type	Swivel caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	154.32 lb
Electric conductive	no
Stainless	no
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	4.09 in
Overall width	0 in
Overall weight	0.32 lb

HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Housing Color	White aluminum (RAL9006)
Offset	1.34 in
Swivel radius	2.91 in
Swivel interference	5.83 in
Dome diameter	0 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	With threadguard
Diameter	3.15 in
Tread width	0.94 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.94 in
Hardness of tread (A)	90 Shore A

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

MONO

5020PJH080L51-10 ~9006/9011/9011

EAN 4031582317114



BETTER MOBILITY. BETTER LIFE.

Product Drawings

