

PRODUCT INFORMATION

NOVATECH

RK.ETP085x90-Ø47x14

EAN 4031582329001



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	85 mm
Tread width	90 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Ball bearing diameter	47 mm
Ball bearing width	14 mm

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.16 kg

NOVATECH

RK.ETP085x90-Ø47x14

EAN 4031582329001

Order number 00828766
Product Drawings



BETTER MOBILITY. BETTER LIFE.

