

NOVATECH

RK.ETP085x90-Ø47x14

EAN 4031582329001



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.16 kg

WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	85 mm
Tread width	90 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Ball bearing diameter	47 mm
Ball bearing width	14 mm

