

ALPHA STAINLESS

8470UOO080P30-11

EAN 4031582370133



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------|
| Roll performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion resistance | ●●●●● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Housing type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 330.69 lb |
| Load capacity Static | 661.39 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 4.25 in |
| Overall weight | 1.41 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 3.15 in |
| Tread width | 1.34 in |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 1.75 in |
| Swivel radius | 3.33 in |
| Swivel interference | 6.65 in |
| Stainless | ✓ |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.43 in |

ALPHA STAINLESS

8470U00080P30-11

EAN 4031582370133



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

8470U00080P30- ϕ 11

