PRODUCT INFORMATION

# ALPHA STAINLESS

8477UFC100P62

EAN 4031582422535



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●●● |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●●● |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Alpha stainless |
| Type | Swivel castor with total lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 160 kg |
| Electric Conductive | No |
| Stainless | Yes |
| Load capacity Static | 320 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall Height | 128 mm |
| Overall weight | 1.01 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Stainless steel |
| Offset | 41 mm |
| Swivel interference | 242 mm |

## WHEEL

| | |
|---|---|
| Tread hardness | soft |
| Body material | Polyamide |
| Tread Material Mix | Elastic tire, non-marking, vulcanized |
| Bearing | Precision ball bearing, stainless |
| Axle | Screwed with nut |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 34 mm |
| Hardness of tread (A) | 64 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Small rectangular plate |
| Plate length | 105 mm |
| Plate width | 80 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Maximum) | 60 mm |
| Plate hole diameter | 9 mm |

© Copyright 2026 TENTE International GmbH

# ALPHA STAINLESS

8477UFC100P62

EAN 4031582422535

BETTER MOBILITY. BETTER LIFE.

## Product Drawings

