

AGILA CARE US

2440XSX150R05-28

EAN 4031582387988



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila care US
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Electric conductive	✓
Load capacity Static	300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	193 mm

WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Precision ball bearing
Offset	50 mm
Swivel radius	125 mm
Swivel interference	250 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm