

PURETECH

PVR 080X35-Ø12 HL44,4

EAN 4031582321241
Order number 00004985



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	80 mm
Tread width	35 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Body width	35 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.164 kg

PRODUCT INFORMATION

PURETECH

PVR 080X35-Ø12 HL44,4

EAN 4031582321241
Order number 00004985



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

