PRODUCT INFORMATION

ZETA

4687FTP125P63 TFR

EAN 4031582390513



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Zeta
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	660 kg
Load capacity at 6 km/h	550 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	164 mm
Overall weight	4.8 kg

HOUSING

Housing Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel Bearing	Two ball races, reinforced or stainless
Housing Color	Blue passivated
Offset	55 mm
Swivel radius	148 mm
Swivel interference	296 mm

WHEEL

Body material	Cast iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	125 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


ZETA

4687FTP125P63 TFR

EAN 4031582390513

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH