

OMIKRON TWIN

9951FTP400P41-400 TFR

EAN 4031582480764



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron twin
Type	Swivel castor with directional lock
Load capacity at 1.8 mph	24250.82 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	22.44 in
Overall weight	544.51 lb

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.15 in
Hardness of tread (A)	92 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	3.54 in
Swivel radius	6.69 in
Swivel interference	13.39 in
	✓

FITTING

Fitting type	Square plate
Plate length	15.75 in
Plate width	15.75 in
Plate hole length (Maximum)	13.39 in
Plate hole width (Maximum)	13.39 in
Plate hole diameter	0.87 in

OMIKRON TWIN

9951FTP400P41-400 TFR

EAN 4031582480764



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

