

NOVATECH

ITP 100x50-Ø20 HL60

EAN 4031582070309



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Aluminium
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ● ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	540 kg
Load capacity at 6 km/h	430 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1080 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.64 kg




PRODUCT INFORMATION

NOVATECH

ITP 100x50-020 HL60

EAN 4031582070809

Order number 00801297



BETTER MOBILITY. BETTER LIFE.