

NOVATECH

FTP 250X80-Ø25 HL92

EAN 4031582319415
Order number 00800997



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Casting |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 9.84 in |
| Tread width | 3.15 in |
| Axle hole diameter | 0.98 in |
| Hub length | 3.62 in |
| Body width | 3.15 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Novatech |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 4761.98 lb |
| Load capacity at 3.7 mph | 3968.32 lb |
| Load capacity Static | 7936.63 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 20.33 lb |

NOVATECH

FTP 250X80-Ø25 HL92

EAN 4031582319415
Order number 00800997



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

