

PRODUCT INFORMATION

NOVATECH

ETX085x85-Ø20 HL95-F

EAN 4031582369649



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |          |
|-----------------------------|----------|
| Product Name                | Novatech |
| Type                        | Wheel    |
| Load capacity at 3 km/h     | 800 kg   |
| Electric Conductive         | No       |
| Stainless                   | No       |
| Load capacity Static        | 1600 kg  |
| Temperature range (Minimum) | -20 °C   |
| Temperature range (Maximum) | 60 °C    |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Steel, iron                    |
| Tread Material Mix    | Polyurethane, casted           |
| Bearing               | Precision ball bearing, sealed |
| Threadguards          | With threadguard               |
| Diameter              | 85 mm                          |
| Tread width           | 85 mm                          |
| Axle Hole Diameter    | 20 mm                          |
| Hub Length            | 95 mm                          |
| Hardness of tread (A) | 92 Shore A                     |
| Sealing type          | F                              |
| Suitable for          | jungheinrich                   |

