

FOOTMASTER

FOOT MASTER GAAD-150-ASF-HUD

EAN 4031582495188



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	630 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	215 mm
Overall width	141 mm
Overall weight	15.19 kg

HOUSING

Offset	35 mm
Swivel radius	115 mm
Swivel interference	230 mm
Dome diameter	128 mm

WHEEL

Bearing	Unmachined hub
Diameter	150 mm
Tread width	35 mm
Body width	35 mm

FITTING

Plate length	145 mm
Plate width	145 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	11 mm

FOOTMASTER

FOOT MASTER GAAD-150-ASF-HUD

EAN 4031582495188

Order number 00800111

Product Drawings



BETTER MOBILITY. BETTER LIFE.

