PRODUCT INFORMATION

# AGILA

2475DYK050P30-11

EAN 4031582344318

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Agila |
| Type | Swivel castor with wheel brake |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | Yes |
| Stainless | No |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 85 °C |
| Overall Height | 69 mm |
| Overall width | 43 mm |
| Overall weight | 0.22 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 24 mm |
| Swivel radius | 82 mm |
| Swivel interference | 164 mm |
| Dome diameter | 41 mm |

## WHEEL

| | |
|---|---|
| Body material | Sheet Steel |
| Tread Material Mix | Solid rubber, black, electric-conductive |
| Bearing | Cone ball bearing |
| Wheel Color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 50 mm |
| Tread width | 19 mm |
| Body width | 19 mm |
| Hardness of tread (A) | 80 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Bolt hole |
| Bolt hole diameter | 11 mm |
| Hint | Castors can be mounted with standard screws of any length. |

© Copyright 2026 TENTE International GmbH

# AGILA

2475DYK050P30-11

EAN 4031582344318

Order number 00005489

**Product Drawings**




